

Flat suction cups, series VP, 5 to 95 mm ø




VP 5 to 10



VP 15 to 25



VP 30 to 95



Applications:

The flat suction cups in series VP are especially recommended for the handling of **flat**, **rigid and smooth** products.

Characteristics:

Models	øΑ	Н	ød	ø D	f	В		Int. volume		Materials NBR SIT5 NR STN FPM NE SIA						Inserts **	
	mm	mm	mm	mm	mm	mm	g	(cm³)	N	NBR		NK	SIN	FPIVI	NE	SIA	page
VP 5	5.5	9	4	7	1	7	0.3	0.03	0.65	0	0					0	74
VP8	7.5	10	5	9	1.3	7	0.4	0.04	1.5	0	0		0			0	74
VP 10	10	10.5	5	9	1.5	7	0.5	0.05	2.2	0	0						74
VP 15	15	11	5	9	2.25	7	0.7	0.18	5.1	0	0						74
VP 20	20	11.5	4.7	10	3	7	1.2	0.44	8.5	0	0	0	0	0			74
VP 25	25	12	4.5	10	3	7	1.4	0.7	13	0	0						74
VP 30	30	19	8	16	2.5	13	4	2.9	22	0	0						75
VP 35	35	20	8	16	3	13	5.6	2.7	32	0	0			0			75
VP 40	40	20	8	16	3	13	9	4	37	0	0						75
VP 50	52	22	8	18	4.5	13	14	7	53	0	0	0	0				75
VP 60	60	22	8	18	4.5	13	16	7.3	80	0	0						75
VP 75	75	32	12	23	4.5	20	33	16	140	0	0	0					76
VP 95	95	38	12	25	12	20	50	47.5	170		0			0	0		76

The values are representative of the mean characteristics of our products.

(*) Fr (in newtons): Actual practical force of the suction cup with a 90% vacuum and a safety factor of 2 inclusive.

(**): Reference of the range and installation diagram for connections.

Materials:

NBR: Nitrile STN: Siton
SIT5: Translucent silicone FPM: Viton
NR: Natural rubber NE: Neoprene

SIA: Antistatic silicone

Special designs:

To meet the specific needs of our customers, our design office develops ranges of special suction cups with special shapes for eggs, paper, CDs, pastries, light bulbs and bags, etc. and of specific materials: Siton, Polyurethane, etc.

For the study of new ranges of special suction cups, we ask our customers to provide us with work specifications, with or without financial contribution. It should be noted that a mould can be designed for quantities of between 500 and 1,000 items per order.

Suction cup sections :

For minimum quantities of 50 pieces, these standard cups can be altered within the parameters of individual cup dimensions.



